



RAT BLOCKER

In acid-proof stainless steel

L811-2 Smart Rat Blocker

A rat blocker should be installed in a sewer line, well or inspection chamber. The rat blocker is made in acid-proof stainless steel and consists of two flaps and a body. The flaps open when the rear flap is affected by the water flow. The product can be installed in both the inlet or outlet side. Our basic package consists of a rat blocker, a mounting grip and a mounting rod. The mounting rod is build in modules, which makes it possible to extend the rod to the needed length.

Product	Article no.	Dimensions		
	L 811-2 Smart Rat Blocker with two flaps i acid-proof stainless steel that only opens when the rear flap is affected by the water flow. Can be mounted in both the inlet and outlet side.	154368111	DN100 mm	DN93-103 mm
		154368161	DN150 mm	DN145-155 mm
154368181		DN180 mm	DN170-180 mm	
154368191		DN190 mm	DN180-190 mm	
154368201		DN200 mm	DN190-200 mm	
154368206		DN205 mm	DN195-205 mm	
154368226		DN225 mm	DN215-225 mm	
				

Advantages:

- ✓ Easy to install
- ✓ Easy to inspect and maintain
- ✓ Free passage of wastewater
- ✓ Comes in Ø110-Ø225 mm pipes

Easy mounting

The system makes it easy to mount the rat blocker.

Free flow design

Designed to maintain the flow along the bottom of the pipe without unnecessary obstruction.

Automatic flaps


Two automatic flaps open only when exposed to the flow of water, helping prevent rats from passing through the pipe.



Accessories:


Mounting rod

Mounting rod with screw and nut. Rods can be connected to achieve the required length



Mounting grip

Fits on top of the mounting rod for easy handling during installation.
Art.no.: 0196443



Accessories for easy installation

The modular mounting system makes it easy to adapt the SMART Rat Blocker installation to different chamber depths. Combine the mounting grip, mounting rods and adapter set to achieve the required installation length and ensure simple handling during installation.

- ✓ Modular mounting system
- ✓ Adjustable to different chamber depths
- ✓ Mounting rods available in multiple lengths
- ✓ Easy installation and handling

Accessories

Product	Article no.	Product no.	Specifications
	L 811-2 Mounting grip is mounted on the top of the mounting rod.	154368501	150 mm
	L 811-2 Mounting rod with screw and nut. The rods can be assembled to achieve the needed length.	154368503	500 mm
		154368502	1000 mm
	L 811-2 Adapter set is mounted on the bottom part of the mounting rod.	154368900	